





























# i AREAS OF APPLICATION

Electrode materials			Clamping system					General accessories	
			ITS-50	ITS-100	System ITS		System 1		
Brass	Copper (2.0060)	Graphite (Q70, Q60, Q40)	Electrode holders		Clamping system accessories	Electrode holders		Clamping system accessories	
	V 91371 V 91570 V 91571	V 9237X V 9258X V 9257X	HER 1112	HER 1412 HER 1472	HER 1672	HER 1840	HER 1212 HER 1272	HER 1840	HER 1118 HER 2320
	V 91381 V 91811	V 9238X	HER 1442	HER 1642	HER 1805	HER 1242			
V 93240 V 93250 V 93255	V 91411 V 93210 V 93220 V 93225	V 93160	HER 1130	HER 1130/SET	HER 1810	HER 1230 HER 1230/SET	HER 1910	V 32910	
	V 93110 V 93120		HER 1132	HER 1132/SET	HER 1812	HER 1232 HER 1232/SET	HER 1912	HWZ 9719	
	V 93140 (WCu)		HER 1134	HER 1134/SET	HER 1850/31			HER 1839	HWZ 9000
	V 91550 V 91552 V 91554 V 91556	V 9255X V 9256X	V 95500 + V 95500 +	HER 1112 HER 1412 HER 1622	HER 1822 HER 1824 HER 1890	V 95500 + HER 1212 HER 1222		V 95500 HER 2320 HER 1840	
	V 91311	V 9231X V 9232X	HER 1472	HER 1672		HER 1272			
	V 91311		HER 1180 + HER 1180 +	HER 1112 HER 1412				HER 1860	
	V 91811	V 9222X	HER 1680 HER 1185 HER 1144	HER 1822 HER 1824	HER 1815				

	Clamping system		General accessories	
	 ITS-50  ITS-100 System ITS	 System 1 System 1		
Measuring and control elements	 HER 2110	 HER 2410   HER 2412	 HER 2160	
	 HER 2112		 HER 2162	
	 HER 2230/30   HER 2230/40	 HER 2530		
Electrode machining	 HER 1118   HER 3010   HER 3030   HER 3040	 HER 3050   HER 3012   HER 3032	 HER 3530   HER 3532	 HER 3534   HER 3535
System adapters	 HER 3080	 HER 3580		
	 HER 3082			