




**PRODUKTBESCHREIBUNG**

- » Schaft ø 3 mm
- » Premium-Gummibindung
- » Sehr hohe Oberflächenqualität



Form		d1	l1	Korn	d3	 Stk./VPE	Nr.	EUR	
A1		Zylinder	3,5	6	80	3	5	V 72525/A1/3,5x 6/ 80	<>
			3,5	6	220	3	5	V 72525/A1/3,5x 6/220	<>
			6	11	80	3	5	V 72525/A1/ 6/x 11/ 80	<>
			6	11	220	3	5	V 72525/A1/ 6/x 11/220	<>
L1		Spitzbogen	3,5	6	80	3	5	V 72525/L1/3,5x 6/ 80	<>
			3,5	6	220	3	5	V 72525/L1/3,5x 6/220	<>
			5,5	10,5	80	3	5	V 72525/L1/5,5x10,5/ 80	<>
			5,5	10,5	220	3	5	V 72525/L1/5,5x10,5/220	<>

**RICHTWERTE**

