




PRODUCT DESCRIPTION

- » Shank ø 3 mm
- » Premium rubber bond
- » Very high surface quality



Shape		d1	l1	Grit	d3	 Pcs./PU	No.	EUR	
A1		Cylinder	3.5	6	80	3	5	V 72525/A1/3,5x 6/ 80	<>
			3.5	6	220	3	5	V 72525/A1/3,5x 6/220	<>
			6	11	80	3	5	V 72525/A1/ 6/x 11/ 80	<>
			6	11	220	3	5	V 72525/A1/ 6/x 11/220	<>
L1		Tree, pointed tip	3.5	6	80	3	5	V 72525/L1/3,5x 6/ 80	<>
			3.5	6	220	3	5	V 72525/L1/3,5x 6/220	<>
			5.5	10.5	80	3	5	V 72525/L1/5,5x10,5/ 80	<>
			5.5	10.5	220	3	5	V 72525/L1/5,5x10,5/220	<>

REFERENCE VALUES

