

PRODUCT DESCRIPTION

- » Humidity sensor with long-term stability
- » Continuous measurement and display of temperature and relative humidity
- » Temperature measuring accuracy of 0.5 °C
- » Calculation and display of the dew point
- » Display of maximum and minimum values
- » Large display



SCOPE OF DELIVERY

- » 9 V block battery, 6F22
- » Calibration protocol

Humidity error limit	Humidity measuring range	Temperature error limit	Temperature measuring range	No.	EUR
± 3 %	10-95 %	0,5 °C	0 bis +50 °C	MTM 1400/608-H1	<>