


PRODUCT DESCRIPTION

- » Shank ø 3 mm
- » Diamond-bonded mounted point
- » Ideal for hardened steels from 60 HRC, HSS and carbides
- » Extremely wear-resistant



	Shape	d3	d1	l1	Grit	No.	EUR	
A1		Cylinder	3	3	6	280	V 72490/A1/ 3x 6/280	<>
			3	6	10	280	V 72490/A1/ 6x10/280	<>
L1		Tree, pointed tip	3	3	6	280	V 72490/L1/ 3x 6/280	<>
			3	5	10	280	V 72490/L1/ 5x10/280	<>