

## PRODUCT DESCRIPTION

- » Replacement item for GESU 1300
- » Quick clamping system
- » Can only be used for the UF-0103 series

Weight	d1	lk	Power	n	No.	EUR
200 g	3	1.5 m	260 W	1,000 - 35,000 min <sup>-1</sup>	GESU 2310/35/ 3	< >



## CHARACTERISTICS

GESU 2310	Value
Motor type	Brushless DC motor
Torque	6.5 Ncm
Concentricity	< 0.02 mm