

PRODUCT DESCRIPTION

- » Easy reading of measured values thanks to rotatable display
- » Incl. cross band probe
- » Large measuring range, briefly up to +500 °C
- » Very fast response time
- » Large display



SCOPE OF DELIVERY

- » 3 AAA microcells

Weight	Response time	Type	Error limit	Scaling	MB	No.	EUR
80 g	ca. 5 sek.	Oberfläche	± 1 °C	0,1 °C	-50 bis +350 °C	MTM 3130/905-T2	<>