


PRODUCT DESCRIPTION


- » 4.3" TFT colour display with speed and load display
- » Automatic type and speed detection of all M-Line micro motor handpieces
- » Infinitely variable speed from 1,000–80,000 min⁻¹
- » Connection options for two handpieces enables efficient working
- » Rotation key for quickly changing the direction of rotation
- » 2x USB port for software updates, for operating USB LED lights (GESM 10006) or for charging USB battery-powered devices



SCOPE OF DELIVERY

- » Control unit (GESM 1000)
- » Micro motor handpiece of your choice (incl. accessories)
- » 2x Handpiece stand (GESM 10003)
- » Mains cable (C13 type F)
- » Safety glasses (ASA 1453)
- » User manual

	Set contents	n max.	No.	EUR
	<ul style="list-style-type: none"> » GESM 1000/80 Control unit » GESM 2001/260/60 Micro motor handpiece, allround, Ø3 mm 	60,000 min ⁻¹	GESM 1000/Set-1	<>
	<ul style="list-style-type: none"> » GESM 1000/80 Control unit » GESM 2007/260/60 Micro motor handpiece, power, Ø3 mm 	60,000 min ⁻¹	GESM 1000/Set-2	<>
	<ul style="list-style-type: none"> » GESM 1000/80 Control unit » GESM 2008/260/60 Micro motor handpiece, long, Ø3 mm 	50,000 min ⁻¹	GESM 1000/Set-3	<>
	<ul style="list-style-type: none"> » GESM 1000/80 Control unit » GESM 2011/260/30/6 Micro motor handpiece, torque, Ø6 mm 	30,000 min ⁻¹	GESM 1000/Set-4	<>
	<ul style="list-style-type: none"> » GESM 1000/80 Control unit » GESM 2012/260/60/3 Micro motor handpiece, collet, Ø3 mm 	60,000 min ⁻¹	GESM 1000/Set-5	<>
	<ul style="list-style-type: none"> » GESM 1000/80 Control unit » GESM 2012/260/60/6 Micro motor handpiece, collet, Ø6 mm 	60,000 min ⁻¹	GESM 1000/Set-6	<>
	<ul style="list-style-type: none"> » GESM 1000/80 Control unit » GESM 2016/260/80 Micro motor handpiece, high speed, Ø3 mm 	80,000 min ⁻¹	GESM 1000/Set-7	<>
	<ul style="list-style-type: none"> » GESM 1000/80 Control unit » GESM 2023/260/30/45 Micro motor angle-type handpiece, 45°, Ø3 mm 	30,000 min ⁻¹	GESM 1000/Set-8	<>
	<ul style="list-style-type: none"> » GESM 1000/80 Control unit » GESM 2023/260/30/90 Micro motor angle-type handpiece, 90°, Ø3 mm 	30,000 min ⁻¹	GESM 1000/Set-9	<>

Set contents	n max.	No.	EUR
 <ul style="list-style-type: none">» Control unit GESM 1000/80» Micro motor handpiece, Mini, ø 3 mm GESM 2004/260/70	70,000 min ⁻¹	GESM 1000/Set-10	<>

 Spare parts and repair by request