


### PRODUCT DESCRIPTION

- » Compact design with low installation height and high clamping forces
- » Simple installation of clamping elements
- » Quick clamping of plates on tables with T-grooves
- » Robust design
- » Inclusive thrust piece



### MATERIAL

- » Forged quenched and tempered alloy steel
- » Black galvanised

h	l3	h2	d	SW	b	l	h1	l1	l2	AMB <sup>1)</sup>	AMS <sup>2)</sup>	SK <sup>3)</sup>	M	b1	No.	EUR
5-38	15-50	61	M12	6	45	65	30	11	-	40	50	22	M12	14	HWS 106/22/12/14	<>
6-68	13-110	86	M16	8	54	135	36	13	25	70	100	30	M12	14	HWS 106/30/12/14	<>
6-68	16-114	86	M16	8	54	135	36	16	28	150	100	30	M16	18	HWS 106/30/16/18	<>
6-50	12-82	78.5	M16	8	54	95	36	12	20	100	100	32	M12	14	HWS 106/32/12/14	<>
6-50	15-95	92	M20	10	60	110	42	15	26	150	150	40	M16	18	HWS 106/40/16/18	<>
5-80	16-134	107	M20	10	60	155	42	16	32	150	150	43	M16	18	HWS 106/43/16/18	<>
7-88	19-165	125	M24	12	75	175	52	19	36	200	220	49	M20	22	HWS 106/49/20/22	<>
8-102	63-180	143	M24	12	90	203	57	22	45	280	300	60	M24	28	HWS 106/60/24/28	<>

1) AMB: tightening torque for fastening screw [Nm]

2) AMS: max. tightening torque for clamping screws [Nm] 3) SK: max. clamping force [kN] at AMS